

Price List Addendum

EFFECTIVE May 1, 2020

Hydraulic Control Valves

Pressure Reducing Valve (250–400 psi)

**VICTAULIC SERIES 972
BERMAD MODEL BC-720-P**

Ductile Iron Body - Epoxy Coated
Y-Pattern
SS 316 Tube/Fitting with SS Control
Accessories
Pressure up to 400 psi



Nominal Size inches	Basic PRV with V-Port (Standard)							
	Grooved (Standard) 400 psi		Female Threaded (NPT) 400 psi		Flanged (ANSI 150) 250 psi		Flanged (ANSI 300) 400 psi	
	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each
1½	S014972H0G	\$3645.50	S014972H0T	\$3915.50	S01497200F	\$3880.50	S014972H0F	\$3995.00
2	S020972H0G	3686.00	S020972H0T	3957.00	S02097200F	3686.00	S020972H0F	4126.00
2½	S024972H0G	3899.50	S024972H0T	4170.50	S02497200F	3899.50	S024972H0F	4368.00
3	S030972H0G	4575.00	S030972H0T	4846.50	S03097200F	4575.00	S030972H0F	5063.00
4	S040972H0G	5403.00	-	-	S04097200F	5403.00	S040972H0F	6160.00
6	S060972H0G	9263.00	-	-	S06097200F	10169.00	S060972H0F	10468.00
8	S080972H0G	12302.00	-	-	S08097200F	13243.00	S080972H0F	13633.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.

Pressure Reducing Valve (250–400 psi)

**VICTAULIC SERIES 972-SS
BERMAD MODEL BC-720-P-SS**

Stainless Steel 316 Body
Stainless Steel 303 Internals
Y-Pattern
SS 316 Tube/Fitting and Control
Accessories
Pressure up to 400 psi



Nominal Size inches	Basic PRV with V-Port (Standard)			
	Flanged (ANSI 150) 250 psi		Flanged (ANSI 300) 400 psi	
	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each
1½	S014972X0F	\$7373.50	S014972XHF	\$11784.50
2	S020972X0F	8663.00	S020972XHF	13446.50
2½	S024972X0F	10894.50	S024972XHF	13518.00
3	S030972X0F	13286.00	S030972XHF	17873.50
4	S040972X0F	15012.00	S040972XHF	28823.00
6	S060972X0F	27499.50	S060972XHF	44459.00
8	S080972X0F	41111.00	S080972XHF	64784.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.

Hydraulic Control Valves

Proportional Pressure Reducing Valve (400 psi)

VICTAULIC SERIES 972-PD BERMAD MODEL BC-720-PD-P

Ductile Iron Body - Epoxy Coated Y-Pattern
SS 316 Tube/Fitting with SS Control Accessories.
Pressure up to 400 psi



Nominal Size	Proportional PRV					
	Grooved (Standard)		Female Threaded (NPT)		Flanged (ANSI 300)	
	inches	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each	Price Each
1½	S014972P0G	\$2439.50	S014972P0T	\$2709.50	S014972P0F	\$2675.00
2	S020972P0G	2481.50	S020972P0T	2752.50	S020972P0F	2803.00
2½	S024972P0G	2694.50	S024972P0T	2966.00	S024972P0F	3037.50
3	S030972P0G	2729.50	S030972P0T	3000.50	S030972P0F	3144.50
4	S040972P0G	3557.50	-	-	S040972P0F	3481.50
6	S060972P0G	7375.50	-	-	S060972P0F	8281.50
8	S080972P0G	10246.50	-	-	S080972P0F	11188.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.

High Pressure Proportional Pressure Reducing Valve (600 psi)

VICTAULIC SERIES 982-PP BERMAD MODEL BC-820-PP-P

Ductile Iron Body - Epoxy Coated Y-Pattern
SS 316 Tube/Fitting with SS Control Accessories
Pressure up to 600 psi



Nominal Size	High Pressure Proportional PRV					
	Grooved (Standard)		Female Threaded		Flanged (ANSI 300)	
	inches	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each	Price Each
1½	S014982P0G	\$7371.50	S014982P0T	\$7695.50	S014982P0F	\$7666.50
2	S020982P0G	7422.50	S020982P0T	7712.50	S020982P0F	7766.00
2½	S024982P0G	7840.00	S024982P0T	8111.00	S024982P0F	8184.00
3	S030982P0G	10507.00	S030982P0T	10778.50	S030982P0F	10922.50
4	S040982P0G	14111.00	-	-	S040982P0F	14694.50
6	S060982P0G	25099.00	-	-	S060982P0F	26005.00
8	S080982P0G	37288.50	-	-	S080982P0F	38230.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.

Hydraulic Control Valves

Check Valve (400 psi)

VICTAULIC SERIES 970-N BERMAD MODEL BC-70N-P

Ductile Iron Body - Epoxy Coated
Y-Pattern
Pressure up to 400 psi

Nominal Size inches	Check Valve, Lift Type					
	Grooved (Standard)		Female Threaded (NPT)		Flanged (ANSI 300)	
	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each	Victaulic Part Code	Price Each
1½	S014970N0G	\$1725.50	S014970N0T	\$1996.00	S014970N0F	\$1962.00
2	S020970N0G	1710.50	S020970N0T	1981.50	S020970N0F	2032.50
2½	S024970N0G	1963.00	S024970N0T	2234.00	S024970N0F	2305.00
3	S030970N0G	3019.50	S030970N0T	3291.50	S030970N0F	3435.00
4	S040970N0G	3445.50	-	-	S040970N0F	3921.00
6	S060970N0G	8035.00	-	-	S060970N0F	8941.00
8	S080970N0G	9753.00	-	-	S080970N0F	10693.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.

Solenoid Control Valve On/Off (400 psi)

VICTAULIC SERIES 971 BERMAD MODEL BC-710-P

Ductile Iron Body - Epoxy Coated
Y-Pattern

24 VAC/Normally Open Valve (Solenoid Energizes to Close)

SS 316 Tube/Fitting with SS
Control Accessories
With Mechanical Limit Switch
Pressure up to 400 psi

Nominal Size inches	Basic Solenoid Control Valve	
	Grooved (Standard)	
	Victaulic Part Code	Price Each
1½	S01497104G	\$4390.50
2	S02097104G	4428.50
2½	S02497104G	4645.00
3	S03097104G	5237.50
4	S04097104G	6023.00
6	S06097104G	9263.00
8	S08097104G	9738.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.



Hydraulic Control Valves

Pressure Reducing Valve with Solenoid Control (400 psi)

**VICTAULIC SERIES 972-55
BERMAD MODEL BC-720-55-P**

Ductile Iron Body - Epoxy Coated
Y-Pattern

**24 VAC/Normally Closed Valve
(Solenoid Energizes to Open)**

SS 316 Tube/Fitting with SS
Control Accessories
With Mechanical Limit Switch
Pressure up to 400 psi



Nominal Size	Basic Solenoid Control Valve	
	Grooved (Standard)	
inches	Victaulic Part Code	Price Each
1½	S014972H5G	\$5978.50
2	S020972H5G	6023.00
2½	S024972H5G	6233.50
3	S030972H5G	6909.50
4	S040972H5G	7165.50
6	S060972H5G	11741.00
8	S080972H5G	14780.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com