

# Price List Addendum

EFFECTIVE June 29, 2020



PL2020-GEN-ADD21

## Roll Grooving Tools – Field Portable

### RG1210

RG1210 is designed for manual grooving of 2-8" | DN50 – DN150 steel. The tool is supplied complete with 2-8" roll sets; Groove confirmation gauges; Adjustable ratchet with swivel handle; and (10) shear pins.



Refer to publication 24.14

Tool Model	Part Number	Tool Weight/ Shipping Weight lb	Rental Per Month	Tool List Price
RG1210 – OGS-200 Groove Profile	R0201210CR	95/153	\$2699.00	\$5792.50

For tool rating capacity please reference publication 24.14.

#### RG1210 PARTS

Description	Part Number	Quantity	Price Each
2 – 3" Upper Roll	R9S2121U03	–	\$204.50
4 – 6" Upper Roll	R9S4121U06	–	198.50
8" Upper Roll	R9S8121U08	–	204.50
2 – 3" Lower Roll	R9S2121L03	–	338.50
4 – 6" Lower Roll	R9S4121L06	–	346.00
8" Lower Roll	R9S8121L08	–	356.00
2" Groove Confirmation Gauge	R020120GGE	–	24.50
2½ – 3" Groove Confirmation Gauge	R024120GGE	–	24.50
4 – 6" Groove Confirmation Gauge	R040120GGE	–	24.50
8" Groove Confirmation Gauge	R080121GGE	–	23.50
Adjustable Ratchet with Swivel Handle	R000120RCH	–	259.50
Shear Pin Punch	R000120PNH	–	31.00
Shear Pin	R000121PIN	10	22.50

#### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

