

Price List Addendum

EFFECTIVE June 22, 2020

Balancing Control Valves

TA Series 7MP

Sizes 2½ – 3” – Ductile Iron

PRESSURE INDEPENDENT BALANCING AND MODULATING CONTROL VALVE

Refer to publication 08.55



TA SERIES 7MP – DUCTILE IRON

Actuator Code Option	Description	Nominal Size inches			
		2½		3	
		Victaulic Part Code	List Price	Victaulic Part Code	List Price
70	SL750/24 Std, 3-pt-24 VAC/VDC	V0247MP070	\$3977.00	V0307MP070	\$4475.00
8A	SL750/24 Adv, 3-pt-24 VAC/VDC-w/o opt board	V0247MP08A	4035.50	V0307MP08A	4035.50
8B	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-TP	V0247MP08B	4217.00	V0307MP08B	4217.00
8C	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus RS485	V0247MP08C	4256.50	V0307MP08C	4256.50
8D	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet RS-485	V0247MP08D	4245.50	V0307MP08D	4245.50
8E	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus/TCP	V0247MP08E	4184.50	V0307MP08E	4184.50
8F	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-IP	V0247MP08F	4184.50	V0307MP08F	4184.50
8G	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet/IP	V0247MP08G	4184.50	V0307MP08G	4184.50
8I	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-TP+Rly	V0247MP08I	4269.00	V0307MP08I	4269.00
8J	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus RS485+Rly	V0247MP08J	4299.50	V0307MP08J	4299.50
8K	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet RS-485+Rly	V0247MP08K	4299.50	V0307MP08K	4299.50
8L	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus/TCP+Rly	V0247MP08L	4238.50	V0307MP08L	4238.50
8M	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-IP+Rly	V0247MP08M	4238.50	V0307MP08M	4238.50
8N	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet/IP+Rly	V0247MP08N	4238.50	V0307MP08N	4238.50
G0	SL750/HV Std, 3-pt-115/230 VAC	V0247MP0G0	4093.50	V0307MP0G0	4093.50
HA	SL750/HV Adv, 3-pt-115/230 VAC-w/o opt board	V0247MP0HA	4332.00	V0307MP0HA	4332.00
HB	SL750/HV Adv, 3-pt-115/230 VAC-KNX-TP	V0247MP0HB	4511.50	V0307MP0HB	4511.50
HC	SL750/HV Adv, 3-pt-115/230 VAC-Modbus RS485	V0247MP0HC	4552.00	V0307MP0HC	4552.00
HD	SL750/HV Adv, 3-pt-115/230 VAC-BACnet RS-485	V0247MP0HD	4542.50	V0307MP0HD	4542.50
HE	SL750/HV Adv, 3-pt-115/230 VAC-Modbus/TCP	V0247MP0HE	4481.00	V0307MP0HE	4481.00
HF	SL750/HV Adv, 3-pt-115/230 VAC-KNX-IP	V0247MP0HF	4481.00	V0307MP0HF	4481.00
HG	SL750/HV Adv, 3-pt-115/230 VAC-BACnet/IP	V0247MP0HG	4481.00	V0307MP0HG	4481.00
HI	SL750/HV Adv, 3-pt-115/230 VAC-KNX-TP+Rly	V0247MP0HI	4566.50	V0307MP0HI	4566.50
HJ	SL750/HV Adv, 3-pt-115/230 VAC-Modbus RS485+Rly	V0247MP0HJ	4595.00	V0307MP0HJ	4595.00
HK	SL750/HV Adv, 3-pt-115/230 VAC-BACnet RS-485+Rly	V0247MP0HK	4595.00	V0307MP0HK	4595.00
HL	SL750/HV Adv, 3-pt-115/230 VAC-Modbus/TCP+Rly	V0247MP0HL	4533.50	V0307MP0HL	4533.50
HM	SL750/HV Adv, 3-pt-115/230 VAC-KNX-IP+Rly	V0247MP0HM	4533.50	V0307MP0HM	4533.50
HN	SL750/HV Adv, 3-pt-115/230 VAC-BACnet/IP+Rly	V0247MP0HN	4533.50	V0307MP0HN	4533.50
MS	TA-MC100 FSE 24V AC/DC -010Vinput 4-20mA, 3-pt	V0247MP0MS	5790.00	V0307MP0MS	6287.00
MT	TA-MC100 FSR 24V AC/DC -010Vinput 4-20mA, 3-pt	V0247MP0MT	5790.00	V0307MP0MT	6287.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com