

Price List Addendum

EFFECTIVE August 5, 2020



PL2020-GEN-ADD26

Grooved IPS Pipe Accessories

Carbon Steel Riser Movement Fitting

NO. A190

Refer to publication 102.90



NO. A190 CARBON STEEL RISER MOVEMENT FITTING

Nominal Size	Approx. Weight Each	Price Each
inches	lb	
2	35.5	\$3501.00
2½	46.9	4083.00
3	57.3	4350.00
4	85.6	5357.00
6	151.4	8682.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Carbon Steel Anchor Outlet Fitting

NO. A191

Refer to publication 102.91



NO. A191 CARBON STEEL ANCHOR OUTLET FITTING

Nominal Size	Approx. Wgt Each	Price Each
inches	lb	
4 x	2	\$2816.00
	2½	2816.00
	3	2816.00
5 x	2	+
	2½	+
	3	+
	4	+
6 x	2	4123.00
	2½	4123.00
	3	4123.00
	4	4123.00
8 x	2	5179.00
	2½	5179.00
	3	5345.00
	4	6135.00
	6	6135.00
10 x	2	7630.00
	2½	7680.00
	3	7729.00
	4	7780.00
12 x	6	8400.00
	2	8567.00
	2½	8604.00
	3	8639.00
	4	8675.00
	6	8747.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.



Equipment Modules

Rigid OGS Carbon Steel Long Run Fittings

Refer to publication 102.40



No. R10



No. R11



No. R12

RIGID OGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. R10			No. R11			No. R12		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
2½	243.90	122.2	\$1166.00	242.40	121.2	\$1166.00	247.65	123.3	\$1235.00
3	244.40	160.2	1404.00	242.65	158.8	1404.00	248.65	162.5	1448.00
4	245.15	228.2	1724.00	243.15	226.7	1724.00	250.15	233.0	1889.00
5	245.65	310.7	2631.00	243.40	307.3	2631.00	251.15	316.8	3003.00
6	246.65	405.4	3248.00	243.65	399.0	3248.00	253.15	413.9	3663.00
8	247.97	615.0	5044.00	244.47	605.5	5044.00	255.72	632.7	6030.00
10	249.20	896.9	8083.00	244.95	871.1	7171.00	258.20	932.6	8593.00
12	250.20	1123.2	8987.00	245.45	1115.9	8152.00	260.20	1182.2	10169.00

RIGID OGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. R13			No. R14			No. R15		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
2½	123.90	64.2	\$899.00	122.40	63.2	\$899.00	127.65	65.3	\$968.00
3	124.40	84.2	1076.00	122.65	82.8	1076.00	128.65	86.5	1120.00
4	125.15	120.2	1273.00	123.15	118.7	1273.00	130.15	125.0	1438.00
5	125.65	164.7	1975.00	123.40	161.3	1975.00	131.15	170.8	2347.00
6	126.65	215.4	2373.00	123.65	209.0	2373.00	133.15	223.9	2788.00
8	127.97	330.0	3732.00	124.47	320.5	3732.00	135.72	347.7	4718.00
10	129.20	491.9	6158.00	124.95	466.1	5246.00	138.20	527.6	6668.00
12	130.20	612.2	6800.00	125.45	604.9	5965.00	140.20	671.2	7982.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Equipment Modules

Flexible OGS Carbon Steel Long Run Fittings

Refer to publication 102.40



No. R20



No. R21



No. R22

FLEXIBLE OGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. R20			No. R21			No. R22		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
2½	244.00	121.6	\$1218.00	242.50	120.6	\$1218.00	247.75	122.7	\$1287.00
3	244.50	159.6	1401.00	242.75	158.2	1401.00	248.75	161.9	1446.00
4	245.38	226.8	1728.00	243.38	225.3	1728.00	250.38	231.6	1893.00
5	245.88	308.5	2697.00	243.63	305.1	2697.00	251.38	314.6	3069.00
6	246.88	403.5	3272.00	243.88	397.1	3272.00	253.38	412.0	3688.00
8	248.13	609.9	5132.00	244.63	600.4	5132.00	255.88	627.6	6118.00
10	249.13	883.8	8007.00	244.88	858.0	7094.00	258.13	919.5	8516.00
12	250.13	1123.8	8919.00	245.38	1116.5	8084.00	260.13	1182.8	10102.00

FLEXIBLE OGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. R23			No. R24			No. R25		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
2½	124.00	63.6	\$951.00	122.50	62.6	\$951.00	127.75	64.7	\$1020.00
3	124.50	83.6	1073.00	122.75	82.2	1073.00	128.75	85.9	1118.00
4	125.38	118.8	1728.00	123.38	117.3	1728.00	130.38	123.6	1893.00
5	125.88	162.5	2397.00	123.63	159.1	2697.00	131.38	168.6	2813.00
6	126.88	213.5	2397.00	123.88	207.1	2397.00	133.38	222.0	2813.00
8	128.13	324.9	3820.00	124.63	315.4	3820.00	135.88	342.6	4806.00
10	129.13	478.8	6082.00	124.88	453.0	5169.00	138.13	514.5	6591.00
12	130.13	612.8	6732.00	125.38	605.5	5897.00	140.13	671.8	7915.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Equipment Modules

AGS™ Rigid AGS Carbon Steel Long Run Fittings

Refer to publication 20.40



No. WR10



No. WR11



No. WR12

RIGID AGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. WR10			No. WR11			No. WR12		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
14	254.25	1291.8	\$11985.00	246.05	1204.0	\$11287.00	262.25	1243.0	\$12927.00
16	256.25	1497.3	11584.00	246.88	1406.8	10317.00	264.25	1436.0	12177.00
18	258.25	1755.3	19410.00	247.71	1612.0	17574.00	267.25	1764.0	20081.00
20	260.25	1966.0	18626.00	248.53	1819.3	16194.00	270.25	2004.0	20115.00
24	264.25	2407.8	29620.00	250.19	2112.5	26413.00	274.25	2351.7	32350.00

RIGID AGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. WR13			No. WR14			No. WR15		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
14	134.25	745.8	\$8310.00	126.05	658.0	\$7612.00	142.25	697.0	\$9252.00
16	136.25	871.3	8697.00	126.88	780.8	7430.00	144.25	810.0	9290.00
18	138.25	1049.3	13198.00	127.71	906.0	11362.00	147.25	1058.0	13869.00
20	140.25	1180.0	13814.00	128.53	1033.3	11382.00	150.25	1218.0	15303.00
24	144.25	1541.8	20958.00	130.19	1246.5	17751.00	154.25	1485.7	23688.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

AGS™ Flexible AGS Carbon Steel Long Run Fittings

Refer to publication 20.40



No. WR20



No. WR21



No. WR22

FLEXIBLE AGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. WR20			No. WR21			No. WR22		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
14	254.31	1290.8	\$11792.00	246.11	1203.0	\$11094.00	262.31	1242.0	\$12734.00
16	256.31	1494.3	11633.00	246.94	1403.8	10366.00	264.31	1433.0	12226.00
18	258.31	1749.3	19488.00	247.77	1606.0	17653.00	267.31	1758.0	20159.00
20	260.31	1966.0	18683.00	248.59	1819.3	16252.00	270.31	2004.0	20172.00
24	264.31	2398.8	29710.00	250.25	2103.5	26504.00	274.31	2342.7	32440.00

RIGID AGS CARBON STEEL LONG RUN FITTINGS

Nom. Size	No. WR23			No. WR24			No. WR25		
	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each	End to End Length	Approx. Wgt. Ea.	Price Each
inches	inches	lb	Painted	inches	lb	Painted	inches	lb	Painted
14	134.31	744.8	\$8117.00	126.11	657.0	\$7419.00	142.31	696.0	\$9059.00
16	136.31	868.3	8746.00	126.94	777.8	7479.00	144.31	807.0	9339.00
18	138.31	1043.3	13276.00	127.77	900.0	11441.00	147.31	1052.0	13947.00
20	140.31	1180.0	13871.00	128.59	1033.3	11440.00	150.31	1218.0	15360.00
24	144.31	1532.8	21048.00	130.25	1237.5	17842.00	154.31	1476.7	23778.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com