

Price List Addendum

EFFECTIVE June 9, 2021




PL2021-GEN-ADD7

Carbon Steel or
Stainless Steel (IPS)
to Copper (CTS)
Dielectric Transition
Fitting

STYLE 647-GT

Refer to publication 22.21




Groove x Thread

STYLE 647-GT – GROOVE X THREAD

PIPE inches		End to End inches	Approx. Wgt. Each		Price Each
Nominal Size	Outside Diameter		lb		
1	1.315	4.10	0.7		\$120.50
1¼	1.660	4.10	1.0		160.50
1½	1.900	4.10	1.1		186.50
2	2.375	4.10	1.5		190.00
2½	2.875	6.10	3.3		255.00
3	3.500	6.10	4.3		456.50
4	4.500	6.10	6.2		610.50

STYLE 647-TT

Refer to publication 22.21



Thread x Thread


STYLE 647-TT – THREAD X THREAD

PIPE inches		End to End inches	Approx. Wgt. Each		Price Each
Nominal Size	Outside Diameter		lb		
½	0.840	3.00	0.2		\$66.50
¾	1.050	3.00	0.3		66.50
1	1.315	4.00	0.6		99.50
1¼	1.660	4.00	0.8		138.50
1½	1.900	4.00	0.9		166.50
2	2.375	4.00	1.2		190.00
2½	2.875	6.00	2.9		255.00
3	3.500	6.00	3.7		456.50
4	4.500	6.00	5.3		610.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

STYLE 647-GG

Refer to publication 22.21



Groove x Groove

STYLE 647-GG – GROOVE X GROOVE

Nominal Size	PIPE inches		End to End inches	Approx. Wgt. Each		Price Each
	Outside Diameter			lb		
	Carbon Steel/ Stainless Steel (IPS)	Copper (CTS)				
2	2.375	2.125	4.19	1.3		\$321.50
2½	2.875	2.625	6.19	3.0		360.00
3	3.500	3.125	6.19	3.9		550.50
4	4.500	4.125	6.19	5.6		1102.50

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

